




NOTES:

1. SUBSTRATE: D263
2. COATING (APPLY ACROSS CLEAR APERTURE):  
R(ABS) < 0.5% @ 450 - 650nm
3. RoHS: COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL: 100mm	 <b>Edmund Optics®</b>		
SHAPE	PLANO	PLANO	BFL: N/A			
SURFACE QUALITY	60 - 40	60 - 40	THIRD ANGLE PROJECTION 	TITLE	100mm FOCAL LENGTH POLARIZATION DIRECTED FLAT LENS	
MIN CLEAR APERTURE	Ø24.50	Ø24.50	ALL DIMS IN	DWG NO	34466	SHEET 1 OF 1
BEVEL MAX FACE	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	mm			