## NOTES:

SHAPE

BEVEL

SURFACE QUALITY

CLEAR APERTURE (mm)

- 1. SUBSTRATE: FUSED SILICA
- 2. S2 TO BE PARALLEL WITH S1 TO WITHIN < 1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) S1 & S2: R(ABS) ≤ 0.25% AT 880nm R(AVG) ≤ 1.25% FROM 400-870nm R(AVG) ≤ 1.25% FROM 890-1000nm

FINE GRIND SURFACE / 4.

5. RoHS COMPLIANT



