





- NOTES:
- 1. SUBSTRATE: POLYMER FILM XP42-18
 - 2. OPERATING TEMPERATURE: -40 TO +80
 - 3. WAVELENGTH RANGE: 400 - 700 nm
 - 4. POLARIZATION: >99.98
 - 5. TRANSMISSION (%):
 - SINGLE: 42 ±2
 - PARALLEL: 36.4
 - CROSSED: <0.004
 - 6. ROHS COMPLIANT



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

 **Edmund Optics®**

THIRD ANGLE PROJECTION 		TITLE	200 x 200mm Linear Polarizing Film (XP42-40)	
ALL DIMS IN	mm	DWG NO	19010	SHEET 1 OF 1