NOTES:

1. SUBSTRATE: SAPPHIRE (AL2O3) DO NOT MANUFACTURE PARTS TO THIS DRAWING


- 2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN ≤ 3.5 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE)


S1 & S2: R(AVG) ≤0.25% @ 880nm R(AVG) ≤1.25% @ 400 - 870nm R(AVG) ≤1.25% @ 890 - 1000nm



FINE GRIND SURFACE

5. ROHS COMPLIANT





SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2		
SHAPE	PLANO	PLANO		
CLEAR APERTURE	Ø22.50	Ø22.50		
SURFACE FLATNESS	2λ	2λ		
SURFACE QUALITY	80-50	80-50		
BIREFRINGENCE (n _o -n _e)	0.008	0.008		
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED		

			Edmund Optics ®			
	THIRD ANGLE PROJECTION	25mm Dia., 0.5mm Thick, VIS-NIR AR Coated Sapphire Window		pated		
Ī	ALL DIMS IN	mm	DWG NO	20810	SHEET 1 OF 1	