

NOTES:

1. SUBSTRATE MATERIAL: Fused Silica
2. SURFACE S2 TO BE PARALLEL TO S1 TO <30 arcsec
3. COATING (APPLY ACROSS CLEAR APERTURE)


S1: Protected Silver (450-10000nm)
R(AVG) >98% @ 450 - 2000nm
R(AVG) >98% @ 2000 - 10,000nm

S2: NONE





FINE GRIND SURFACE

5. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	 Edmund Optics®				
SHAPE	PLANO	PLANO					
SURFACE QUALITY	20 - 10	COMMERCIAL POLISH					
SURFACE FLATNESS	$\lambda/10$	N/A	THIRD ANGLE PROJECTION		TITLE	25 x 35mm Protected Silver Coated, $\lambda/10$ Mirror	
CLEAR APERTURE	22.50 X 31.50	N/A			DWG NO	25549	SHEET 1 OF 1
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN		mm		