


NOTES:

- 1. SUBSTRATE:  
FUSED SILICA
- 2. SURFACE S2 TO BE PARALLEL WITH S1 TO 30 ARCSEC
- 3. COATING (APPLY ACROSS CLEAR APERTURE)

S1:Ravg >89% @ 250 - 450nm  
Ravg >85% @ 250 - 700nm  
S2:NONE

4. FINE GRIND SURFACE


- 5. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® Edmund Optics®

	S1	S2	THIRD ANGLE PROJECTION 		TITLE	10mm Diameter, 1mm Thick, Diameter UV Enhanced Aluminum Coated, λ/10 Mirror	DWG NO 26102	SHEET 6 OF 28
SURFACE QUALITY	20-10	COMMERCIAL POLISH						
SURFACE FLATNESS	λ/10 (Measured Pre-Coating)	N/A	ALL DIMS IN mm					
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED						