


NOTES:

- 1. SUBSTRATE:
FUSED SILICA
- 2. SURFACE S2 TO BE PARALLEL WITH S1 TO 30 ARCSEC
- 3. COATING (APPLY ACROSS CLEAR APERTURE)

S1:Ravg >95% @ 450 - 650nm
S2:NONE

4. FINE GRIND SURFACE


5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

 Edmund Optics®

	S1	S2	THIRD ANGLE PROJECTION 		TITLE	15mm Diameter, 1.5mm Thick, Enhanced Aluminum Coated, λ/10 Mirror	
SURFACE QUALITY	20-10	COMMERCIAL POLISH					
SURFACE FLATNESS	λ/10 (Measured Pre-Coating)	N/A	ALL DIMS IN mm		DWG NO	26367	SHEET 13 OF 28
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED					