


NOTES:

- 1. SUBSTRATE:
FUSED SILICA
- 2. SURFACE S2 TO BE PARALLEL WITH S1 TO 30 ARCSEC
- 3. COATING (APPLY ACROSS CLEAR APERTURE)

S1:Ravg >96% @ 700 - 2000nm
Ravg >96% @ 2000 - 10,000nm
S2:NONE

4. FINE GRIND SURFACE

- 5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]

	S1	S2	THIRD ANGLE PROJECTION		TITLE	15mm Diameter, 1.5mm Thick, Diameter Protected Gold Coated, λ/10 Mirror	DWG NO	26369	SHEET 15 OF 28
SURFACE QUALITY	20-10	COMMERCIAL POLISH							
SURFACE FLATNESS	λ/10 (Measured Pre-Coating)	N/A	ALL DIMS IN		mm				
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED							