


NOTES:

- 1. SUBSTRATE:  
FUSED SILICA
- 2. SURFACE S2 TO BE PARALLEL WITH S1 TO 30 ARCSEC
- 3. COATING (APPLY ACROSS CLEAR APERTURE)  
  
S1:Ravg >95% @ 450 - 650nm  
S2:NONE

4. FINE GRIND SURFACE


5. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO<sup>®</sup> Edmund Optics<sup>®</sup>**

	S1	S2	THIRD ANGLE PROJECTION 		TITLE	20mm Diameter, 2mm Thick, Enhanced Aluminum Coated, λ/10 Mirror	DWG NO 26371	SHEET 17 OF 28
SURFACE QUALITY	20-10	COMMERCIAL POLISH						
SURFACE FLATNESS	λ/10 (Measured Pre-Coating)	N/A	ALL DIMS IN mm					
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED						