




NOTES:

- 1. SUBSTRATE:
FLOAT GLASS
- 2. COATING (APPLY ACROSS CLEAR APERTURE)
S1: PROTECTED SILVER (450-10,000nm)
R(AVG) >98% @ 450 - 800nm @ 0° AOI
R(AVG)>98.5% @ 2000 - 10,000nm @ 0° AOI
- S2: NONE



3. FINE GRIND SURFACE

- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	 Edmund Optics®			
SHAPE	PLANO	PLANO				
SURFACE QUALITY	60 - 40	N/A				
SURFACE FLATNESS	4 - 6λ	N/A				
CLEAR APERTURE	76.50 x 108.00	N/A				
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED				
			ALL DIMS IN	mm	TITLE	85 x 120mm Silver, 4-6λ Mirror
			DWG NO			71426
						SHEET 8 OF 9